



Representative Image

Catalog No. 18RA-2577

Description: FULLY INS NYLON FEM DISCONNECT

UPC No 786210839332

Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect

Nylon Fully Insulated Female Disconnect, Length 1.01 Inches, Width 0.38 Inch, Maximum Insulation 0.165, Tab Size 0.25x0.032, Wire Range 22-18 AWG, Color Red, Brass, Tin Plated, 50 Pack

Descriptors

Category	Wire terminal disconnect
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

Specifications

Material	Brass
Finish	Tin Plated
Color	Red
Insulation	Nylon/Polyamide

Classifications

Brand Name	Sta-Kon
Standard	UL E66716

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Fully isolated
Colour insulation	Red
Material insulation	PA
Material	Brass
AWG-range	22-18

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622701	N/A	N/A	N/A
CSA	7222	622701	N/A	N/A	N/A
UL	E66716	N/A	N/A	N/A	N/A