



Representative Image

Alternat Catalog No. 2 GC Catalog No. 2GC

Description: 2 GANG BX CVR,13/16 RSD,8.5 CU-IN

UPC No 785991128659

Home > Boxes & Commercial Fittings > Steel City > Cover for box/housing for built-in mounting in the wall/ceiling

Two Gang Box Cover, 8.5 Cubic Inches, 7 Inches Long x 4-11/16 Inches Wide x 13/16 Inches Raised for Plaster, Galvanized Steel, Holes between Gangs are Spaced on 13/16 Inch Centers, Tapped Holes in Ears, Spaced on 3-9/32 Inches Centers to Accommodate All Standard Receptacles and Switches, Furnished with Extra Plugged Screw Holes, if these Screw Holes are Used, the Cover will fit the Next Smaller Size Box

Descriptors

Category	Cover for box/housing for built-in mounting in the wall/ceiling
Special Features	Holes between gangs are spaced on 1-3/16 inch centers.
Application	The cover will fit the next smaller size box

Specifications

Material	Steel
Finish	Pre-galvanized
Number Of Outlet	2
Knockouts	0
Cubic Capacity	8.5 cu in

Classifications

Brand Name	Steel City
Standard	UL E2969

Dimensions

Size	7 Inches Length x 4-11/16 Inches Width
------	--

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	12798	441302	N/A	1352977_2017-05-26	N/A
UL	E2969	N/A	QCIT	N/A	N/A