



Representative Image

Catalog No. 4-MB

Description: MASONRY BOX 3-1/2 INCH DEEP, 4 GANG

UPC No 781720004966

Home > Boxes & Commercial Fittings > Steel City > Masonry box

Four Gang Masonry Box, 93.5 Cubic Inches, 3-3/4 Inches Long x 7-3/8 Inches Wide x 3-1/2 Inches Deep, 1/2 Inch and 3/4 Inch Concentric Knockouts, Galvanized Steel, Welded Construction, For use with Conduit

Descriptors

Category	Masonry box
Application	For use with conduit

Specifications

Number Of Outlet	4
Material	Steel
Color	Silver
Construction	Welded
Cubic Capacity	93.5 cu in
Knockouts	20

Classifications

Brand Name	Steel City
Standard	UL E2969

Dimensions

Size	3-3/4 Inches Length x 7-3/8 Inches Width x 3-1/2 Inches Depth
------	---

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Assembly arrangement	Surface mounted housing
Mounting direction	Horizontal
Material	Metal

by ABB

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Colour	Silver
Transparent	N
Width of device	187.325 mm

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E2969	N/A	QCIT	N/A	N/A