



Catalog No. AB20-M20

Description: M20 ADAPTOR BODY FOR NC20 BLACK

UPC No 5020963022388

Home > Boxes & Commercial Fittings > Steel City / Iberville > Electrical fittings

Sealed Conduit Fitting, Straight, Compression Type, Conduit Size NC20/NW17, M20 Thread, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP67, 68 Rating, Very High UV Protection, Polyamide (Nylon), Black

Descriptors

| | |
|------------------|--|
| Category | Electrical fittings |
| Special Features | Self Extinguishing, Low Smoke Toxicity, and Halogen Free |
| Application | Designed to Help Maintain System Integrity for Conduit Systems |

Specifications

| | |
|--------------------|----------------------|
| Material | Polyamide/Nylon |
| Insulation Class | IP67, IP68 |
| Color | Black |
| Connection | Straight, M20 thread |
| Temperature Rating | -40 to 120 C |

Classifications

| | |
|------------|---|
| Brand Name | Harnessflex |
| Standard | ADR Approved (with NC conduits only) , RoHS |

Dimensions

| | |
|------|-------------------------------------|
| Size | Conduit Size NC20/NW17 , M20 Thread |
|------|-------------------------------------|

Compliance and Certifications

| | |
|------|-----------------|
| RoHS | RoHS3 Compliant |
|------|-----------------|

| | |
|---------------------------|---|
| ETIM | EC001176 Screw connection for corrugated plastic hose |
| Nominal diameter | 20 mm |
| Degree of protection (IP) | IP68 |
| Model | Straight |
| Construction type | External thread |
| Type of connection | Thread |

by ABB

| | |
|------------------------|---|
| ETIM | EC001176 Screw connection for corrugated plastic hose |
| Thread type | Metric |
| Thread connection size | M20 x 1.5 |
| Thread length | 14 mm |
| Thread length | 0.551 inch |
| Total length | 30 mm |
| Total height | 39 mm |
| Material | Polyamide (PA) |
| Colour | Black |