



Representative Image

**Catalog No. CIH08-90-AT4PL**

**Description: 4WAY 90D INTERFACE NC08 AMP PLUG**

**UPC No 5020963804878**

**Home > Cable Protection Systems > Harnessflex > Electrical connector assembly**

Hinged Connector Interface Fitting for High Temperatures, 90 Degree Elbow, 4-Way Ampseal Automotive Connector to Conduit, Conduit Size NC08/NW7.5, Standard Profile Back Shell for Ampseal Plug, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

**Descriptors**

Category	Electrical connector assembly
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit

**Specifications**

Connection	90 degree elbow, 3-way connection
Material	Polyamide/Nylon
Color	Dark Orange
Insulation	IP40
Temperature Rating	-40 to 185 C
Environmental Conditions	Very High UV Protection

**Classifications**

Brand Name	Harnessflex
Standard	RoHS Compliant

**Dimensions**

Size	Conduit Size NC08/NW7.5
------	-------------------------

**Compliance and Certifications**

RoHS	RoHS3 Compliant
------	-----------------