



Catalog No. CIH12-90-FCI04

Description: HIGH TEMP ELBOW APEX FCI04 - NC12

UPC No 5020963805325

Home > Cable Protection Systems > Harnessflex > Electrical connector assembly

Hinged Connector Interface Fitting for High Temperatures, 90 Degree Elbow, 4-Way FCI APex Automotive Connector to Conduit, Conduit Size NC12/NW10, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

Descriptors

Category	Electrical connector assembly
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit

Specifications

Connection	90 degree elbow, 3-way connection
Material	Polyamide/Nylon
Color	Dark Orange
Insulation	IP40
Temperature Rating	-40 to 185 C
Environmental Conditions	Medium UV Protection

Classifications

Brand Name	Harnessflex
Standard	RoHS Compliant

Dimensions

Size	Conduit Size NC12/NW10
------	------------------------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------