



## Catalog No. CIH12-AT8PL

**Description:** HIGH TEMP INTERFACE NC12 - AMPS 8

**UPC No** 5020963804656

**Home > Cable Protection Systems > Harnessflex > Electrical connector assembly**

Hinged Connector Interface Fitting for High Temperatures, Straight, 8-Way Ampseal Automotive Connector to Conduit, Conduit Size NC12/NW10, Standard Profile Back Shell for Ampseal Plug, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

### Descriptors

Category	Electrical connector assembly
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit

### Specifications

Connection	Straight, 8-way connection
Material	Polyamide/Nylon
Color	Dark Orange
Insulation	IP40
Temperature Rating	-40 to 185 C
Environmental Conditions	Very High UV Protection

### Classifications

Brand Name	Harnessflex
Standard	RoHS Compliant

### Dimensions

Size	Conduit Size NC12/NW10
------	------------------------

### Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------