



Representative Image

**Catalog No. CIH12-FCI04**

**Description:** HIGH TEMP APEX FCI04 - NC12

**UPC No** 5020963805240

**Home > Cable Protection Systems > Harnessflex > Electrical connector assembly**

Hinged Connector Interface Fitting for High Temperatures, Straight, 4-Way FCI APex Automotive Connector to Conduit, Conduit Size NC12/NW10, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

**Descriptors**

|                  |  |
|------------------|--|
| Category         | Electrical connector assembly                              |
| Special Features | High Pull-Off Strength                                     |
| Application      | Provide Connection Between Connector Interface and Conduit |

**Specifications**

|                          |                            |
|--------------------------|----------------------------|
| Connection               | Straight, 4-way connection |
| Material                 | Polyamide/Nylon            |
| Color                    | Dark Orange                |
| Insulation               | IP40                       |
| Temperature Rating       | -40 to 185 C               |
| Environmental Conditions | Medium UV Protection       |

**Classifications**

|            |                |
|------------|----------------|
| Brand Name | Harnessflex    |
| Standard   | RoHS Compliant |

**Dimensions**

|      |                        |
|------|------------------------|
| Size | Conduit Size NC12/NW10 |
|------|------------------------|

**Compliance and Certifications**

|      |                 |
|------|-----------------|
| RoHS | RoHS3 Compliant |
|------|-----------------|