

Representative Image

Catalog No. CPS341212

Description: CONNECTOR SHROUD(341212)

UPC No 5020963036484

Home > Cable Protection Systems > Adaptaflex > Electrical conduit coupling

Hinged Protective Shroud, Straight, Conduit Size A: NC12/NW10, Side B: NC12/NW10, Internal Diameter 35mm, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

Descriptors

Category	Electrical conduit coupling
Application	Protection for In-Line Connectors, Fuse Links, Circuit Breakers and Splicing Areas

Specifications

Installation Type	Externally Hinged
Material	Polyamide/Nylon
Color	Black

Classifications

Brand Name	Harnessflex
Standard	RoHS Compliant, Complies with End of Life Vehicle (ELV) Directive EU 2000/53/EC

Dimensions

Trade Size	NC12/NW10
Inside Diameter	35 mm

Compliance and Certifications

RoHS	RoHS3 Compliant

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP40
Model	Straight
Nominal size	12-12 mm
Colour	Black

by ABB