



Catalog No. CTPA12-S/100M

Description: 12MM SLIT PA6 CONDUIT 100M - BL

UPC No 5020963022319

Home > Cable Protection Systems > Harnessflex > Flexible Non-Metallic Conduit

Lightweight Weight, Extra Flexible Slit Conduit, NC Size 12/NW Size 10, Outside Diameter 13.0mm, Inside Diameter 10.1mm, Static Bend Radius 20mm, High Fatigue Life and Abrasion, Impact Resistance, IP40 Rating, Polyamide 6, Reel Length 100 Meters, Black

Descriptors

Category	Flexible Non-Metallic Conduit
Special Features	Self Extinguishing, Low Smoke Toxicity & Halogen Free
Application	General Purpose, Lightweight Loom Applications

Specifications

Radius	Static: 20 mm
Flexibility	High
Material	Polyamide/Nylon 6
Color	Black

Classifications

Brand Name	Harnessflex
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV) EU200/53/EC

Dimensions

Trade Size	NC12/NW10
Outside Diameter	13 mm
Inside Diameter	10.1 mm
Length	100 m

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	12 mm
Nominal size in inch	5/16 inch
Outer diameter	13 mm
Inner diameter	10.1 mm
Material	Polyamide 6
Degree of protection (IP)	IP40
Fire resistance in accordance with UL94	HB
Bending radius, static	20 mm
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	Y
Halogen free	Y