



Catalog No. DS2505FRAB0

Description: 200A,REC,4P5W,MG,505,AB0,3P250/440

UPC No 708917313793

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Receptacle with Angle Adapter and Junction Box, 200 Amp, 4 Pole 5 Wire, 30 250/440V, 50Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Electrical hook-up of mobile medical imaging (MMI trailers).

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	200 Amps
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

FTIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Number of poles	4

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E2630	N/A	QLIW	N/A	N/A