



Representative Image

Catalog No. EPH08S08

Description: HIGH TEMP ELBOW NC08 - NC08

UPC No 5020963804410

Home > Cable Protection Systems > Harnessflex > Electrical conduit elbow

Hinged Conduit Joiner for High Temperatures, 90 Degree Elbow, Conduit Size NC08/NW7.5 to NC08/NW7.5, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

Descriptors

Category	Electrical conduit elbow
Special Features	One-Piece External Design for Unrestricted Bore and Quick Assembly with No Tools
Application	Designed to Snap Together Over All Types of Slit and Unslit Conduit, Maintaining Maximum Conduit Bore

Specifications

Material	High Temperature Polyamide/Nylon
Color	Dark Orange
Flexibility	Rigid

Classifications

Brand Name	Harnessflex
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV) EU200/53/EC

Dimensions

Size	NC08/NW7.5 to NC08/NW7.5
------	--------------------------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP40
Model	Corner piece
Nominal size	8-8 mm
Colour	Other


by ABB