

Representative Image

Catalog No. NC10-S/100M

Description: 10MM SLIT PA6 CONDUIT 100M - BL

UPC No 5020963023880

Home > Cable Protection Systems > Harnessflex > Flexible Non-Metallic Conduit

Standard Weight, General Purpose Slit Conduit, NC Size 10/NW Size 8.5, Outside Diameter 11.5mm, Inside Diameter 8.4mm, Static Bend Radius 15mm, High Flexibility and Fatigue Life, IP40 Rating, Polyamide 6, Reel Length 100 Meters, Black

Descriptors

Category	Flexible Non-Metallic Conduit
Application	General Purpose

Specifications

Radius	Static: 15 mm
Flexibility	Very High
Material	Polyamide/Nylon 6
Color	Black

Classifications

Brand Name	Harnessflex
Standard	ADR Approved, RoHS, Conforms with End of Life Vehicle Directive (ELV)EU200/53/EC

Dimensions

Trade Size	NC10/NW8.5
Outside Diameter	11.5 mm
Inside Diameter	8.4 mm
Length	100 m

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM Classification

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	10 mm

by ABB

ETIM	EC001175 Corrugated plastic hose
Nominal size in inch	1/4 inch
Outer diameter	11.5 mm
Inner diameter	8.4 mm
Material	Polyamide 6
Degree of protection (IP)	IP40
Fire resistance in accordance with UL94	HB
Bending radius, static	15 mm
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	Y
Halogen free	Y