



## Catalog No. TPH201616

**Description:** HIGH TEMP T PIECE NC 20-16-16

**UPC No** 5020963805660

**Home > Cable Protection Systems > Harnessflex > Electrical conduit elbow**

Hinged Conduit Joiner for High Temperatures, T-Shape, Conduit Size A: NC20/NW17, Size B: NC16/NW13, Size C: NC16/NW13, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

### Descriptors

Category	Electrical conduit elbow
Special Features	Can Be Use as an In-Line Reducer as well as Enlarger
Application	Designed to Snap Together Over All Types of Slit and Unslit Conduit, Maintaining Maximum Conduit Bore

### Specifications

Material	High Temperature Polyamide/Nylon
Color	Dark Orange
Flexibility	Rigid

### Classifications

Brand Name	Harnessflex
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV) EU200/53/EC

### Dimensions

Size	Conduit Sizes A: NC20/NW17, B: NC16/NW13, C: NC16/NW13
------	--------------------------------------------------------

### Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP40
Model	T-piece
Nominal size	16-20 mm
Colour	Other