



**Catalog No. YPH121208**

**Description: HIGH TEMP Y PIECE NC 12-12-08**

**UPC No 5020963805851**

**Home > Cable Protection Systems > Harnessflex > Electrical conduit elbow**

Hinged Conduit Joiner for High Temperatures, Y-Shape, Conduit Size A: NC12/NW10, Size B: NC12/NW10, Size C: NC08/NW7.5, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

**Descriptors**

Category	Electrical conduit elbow
Special Features	Can Be Use as an In-Line Reducer as well as Enlarger
Application	Designed to Snap Together Over All Types of Slit and Unslit Conduit, Maintaining Maximum Conduit Bore

**Specifications**

Material	High Temperature Polyamide/Nylon
Color	Dark Orange
Flexibility	Rigid

**Classifications**

Brand Name	Harnessflex
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV) EU200/53/EC

**Dimensions**

Size	Conduit Sizes A: NC12/NW10, B: NC12/NW10, C: NC08/NW7.5
------	---

**Compliance and Certifications**

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP40
Model	Y-piece
Nominal size	12-12 mm
Colour	Other