



Catalog No. M055G

Description: 70A SURFACE MTRD 50/20

UPC No 784567565300

Home > Temporary Power > Temporary Power

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

Descriptors

Category	Temporary Power
----------	-----------------

Specifications

Mounting	Surface
Heads	1
Metering	Ring-Type
Receptacles	14-50WR(BR54UWR) 5-20WR2
Feed	Overhead
AIC	10,000
Amps	70.0 A
Cabinet Size	9 X 30
Circuit Protection	Yes
Hub Provision	Yes
Installed Breaker	CB250 GFI120
Load Center	LC33N1
Loop Feed	No
Phase	1
Suitable for Service Equipment	No
Unit Weight	25.0 lb
Volts	120/240

Classifications

Standard Package	1
Stock Class Code	Stock

Approvals

Certification	UL/CUL
---------------	--------

