



Catalog No. M354C

Description: 100A SURFACE MTRD 50A RECEPTACLE

UPC No 784567565904

Home > Power Outlets

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

Descriptors

Category	Power Outlets
----------	---------------

Specifications

Mounting	Surface
Heads	1
Metering	Ring-Type
Receptacles	14-50WR(BR54UWR)
Feed	Overhead
AIC	10,000
Amps	100 A
Cabinet Size	9 in. W X 30 in. H
Circuit Protection	Breaker
Hub Provision	Yes
Installed Breaker	CB250 SPACE (3) CB120
Load Center	LC33N1
Loop Feed	Yes
Phase	1
Suitable for Service Equipment	No
Unit Weight	25 lb
Volts	120/240

Classifications

Standard Package	1
Stock Class Code	Non Stock

Approvals

Certification	UL/CUL
---------------	--------