



Catalog No. R058CP6

Description: 80A POST MTRD 50/30

UPC No 784567620801

Home > Power Outlets

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

Descriptors

Category	Power Outlets
----------	---------------

Specifications

Mounting	Pedestal - Earth Burial
Heads	1
Metering	Ringless
Receptacles	14-50WR(BR54UWR) BR32UWR
Feed	Underground
AIC	10,000
Amps	80 A
Cabinet Size	9 in. W x 77.5 in. H
Circuit Protection	Breaker
Hub Provision	No
Installed Breaker	CB250 CB130
Load Center	LC33N1
Loop Feed	Yes
Phase	1
Suitable for Service Equipment	No
Unit Weight	59 lb
Volts	120/240

Classifications

Standard Package	1
Stock Class Code	Non Stock

Approvals

Certification	UL/CUL
---------------	--------