



Representative Image

Catalog No. THQMV150WL

Description: 150A PMGOLD L/C MAIN BKR

UPC No 783164163209

Home > Circuit Breakers

PowerMark Gold Main Circuit Breakers for use with 150A-225A PowerMark Gold Load Centers (Includes mounting base). Main Circuit Breaker Kits 22,000 AIC. 60 C / 75 F Conductor Rating. Box Type Terminals. Quick-Make, Quick-Break. Multi-pole Breakers Incorporate Internal Common Trip. UL Listed. 00WL 2 A

Descriptors

Category

Circuit Breakers

Specifications

Type	Q-Line Plug-In
Poles	2
Amperage	150 A
Voltage	240 V
Interruption Rating	22kAIC
Plug-In Type	1"
AIC	22000

Classifications

UL/CUL Listing

UL/CUL