



**Catalog No. THQMV150WL**

**Description: 150A PMGOLD L/C MAIN BKR**

**UPC No 783164163209**

**Home > Circuit Breakers**

PowerMark Gold Main Circuit Breakers for use with 150A-225A PowerMark Gold Load Centers (Includes mounting base). Main Circuit Breaker Kits 22,000 AIC. 60 C / 75 F Conductor Rating. Box Type Terminals. Quick-Make, Quick-Break. Multi-pole Breakers Incorporate Internal Common Trip. UL Listed. 00WL 2 A

**Descriptors**

|          |                  |
|----------|------------------|
| Category | Circuit Breakers |
|----------|------------------|

**Specifications**

|                     |                |
|---------------------|----------------|
| Type                | Q-Line Plug-In |
| Poles               | 2              |
| Amperage            | 150 A          |
| Voltage             | 240 V          |
| Interruption Rating | 22kAIC         |
| Plug-In Type        | 1"             |
| AIC                 | 22000          |

**Classifications**

|                |        |
|----------------|--------|
| UL/CUL Listing | UL/CUL |
|----------------|--------|