



## Catalog No. U041010

**Description:** MW 30A SURF UNMTRD 30/20GFCI

**UPC No** 784567302158

**Home > Power Outlets**

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

### Descriptors

Category	Power Outlets
----------	---------------

### Specifications

Mounting	Surface
Heads	1
Metering	Unmetered
Receptacles	TT-30WR(PR32UWR) 5-20WR2GFCI
Feed	Overhead
AIC	10,000
Amps	30 A
Cabinet Size	6 in. W X 9 in. H
Circuit Protection	None
Hub Provision	Yes
Installed Breaker	None
Load Center	None
Loop Feed	No
Phase	1
Suitable for Service Equipment	No
Unit Weight	9 lb
Volts	120/240

### Classifications

Standard Package	4
Stock Class Code	Non Stock

### Approvals

Certification	UL/CUL
---------------	--------