



Catalog No. U132CB6

Description: 70A B/B POST UNMTRD 30 2SP

UPC No 784567560855

Home > Power Outlets

Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism, and normal field use.

Descriptors

Category	Power Outlets
----------	---------------

Specifications

Mounting	Pedestal - Earth Burial
Heads	2
Metering	Unmetered
Receptacles	TT-30WR(PR32UWR)
Feed	Underground
AIC	10,000
Amps	70 A
Cabinet Size	6.5 in. W x 62 in. H
Circuit Protection	Breaker
Hub Provision	No
Installed Breaker	CB130
Load Center	LC33N1
Loop Feed	Yes
Phase	1
Unit Weight	9 lb
Volts	120/240

Classifications

Stock Class Code	Non Stock
------------------	-----------

Approvals

Certification	UL/CUL
---------------	--------