



Representative Image

## Catalog No. UG412RMW250

**Description:** MW GFI DISCONNECT SPA PANEL 50A

**UPC No** 784567206487

**Home > Spa / Main Generating Panels > Spa Panels**

GFI disconnects provide a convenient, low-cost means to satisfy NEC requirements for spas, hot tubs, water heaters, and swimming pools. The NEMA 3R design insures a safe, weather-tight installation for residential, light commercial, and even some industrial applications.

### Descriptors

|          |            |
|----------|------------|
| Category | Spa Panels |
|----------|------------|

### Specifications

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Amps                           | 50                                         |
| Enclosure                      | Metallic                                   |
| AIC                            | 10,000                                     |
| Cabinet Size                   | 7 in. W X 10 in. H                         |
| Color                          | Gray                                       |
| Hub Provision                  | Yes                                        |
| Installed Breaker              | 2P 50A GFI                                 |
| Load Center                    | 125A Rated; w/ 2 additional breaker spaces |
| Phase                          | 1                                          |
| Suitable for Service Equipment | No                                         |
| Wire Range                     | 6-2/0                                      |
| Unit Weight                    | 8 lb                                       |
| Volts                          | 120/240                                    |

### Classifications

|                  |       |
|------------------|-------|
| Standard Package | 1     |
| Stock Class Code | Stock |

### Approvals

|               |        |
|---------------|--------|
| Certification | UL/CUL |
|---------------|--------|