



Representative Image

## Catalog No. 1SAJ622000R0101

Description: DX122-FBP.0 IO-Module for UMC100 DI 110/230VAC, supply 24VDC

UPC No 4013614403729

Home > Controls & Protective Relays > UMC

### Descriptors

Category	UMC
----------	-----

### Specifications

Product Type	Accessories
Product Name	FBP Module
Rated Control Supply Voltage	24 V DC
Ambient Air Temperature	Storage -25 ... +70 degree Celsius Operation 0 ... +55 degree Celsius
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 3 ... 150 Hz
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 150 m / s2
RoHS Status	Following EU Directive 2011/65/EU
Analog Inputs	0

### Dimensions

Product Net Width	45 mm
Product Net Height	78 mm
Product Net Depth / Length	102 mm
Product Net Weight	0.22 kg

### Package Information

Package Level 1 Units	1 piece
Package Level 1 Width	45 mm
Package Level 1 Height	78 mm
Package Level 1 Depth / Length	102 mm
Package Level 1 Gross Weight	0.22 kg
Package Level 1 EAN	4013614403729

### Ordering

Minimum Order Quantity	1
------------------------	---


  
**by ABB**

## Ordering

Customs Tariff Number	85364900
ECCN	N
ECN	N
Analog Outputs	1