

**Catalog No. 1SAJ929200R0060**
**Description: CEM11-FBP.60 Earth Leakage Monitor 60 mm Ø, setting 0.12 ... 6.8 A**
**UPC No 4013614388620**
**Home > Controls & Protective Relays > UMC**

CEM11-FBP.60 Earth Leakage Monitor 60



Representative Image

**Descriptors**

Category	UMC
----------	-----

**Specifications**

Product Name	Earth Leakage Monitor
Rated Control Supply Voltage	24 V DC
Ambient Air Temperature	Storage -40 ... +75 degree Celsius Operation 0 ... +60 degree Celsius
RoHS Status	Following EU Directive 2011/65/EU

**Dimensions**

Product Net Width	135 mm
Product Net Height	38 mm
Product Net Depth / Length	116 mm
Product Net Weight	334 gram

**Package Information**

Package Level 1 Units	1 piece
Package Level 1 Width	135 mm
Package Level 1 Height	38 mm
Package Level 1 Depth / Length	116 mm
Package Level 1 Gross Weight	0.334 kg
Package Level 1 EAN	4013614388620

**Ordering**

Minimum Order Quantity	1
Customs Tariff Number	85043129
ECCN	N
ECN	N