

Alternate Catalog No. DB45EF Catalog No. 1SAX201910R0001

Description: DB45EF Single Mounting Kit

UPC No 4013614493393

Home > Contactors & Starters > Overload Relays

DB45EF Single Mounting Kit for EF45



Representative Image

Descriptors

Category	Overload Relays
----------	-----------------

Specifications

Product Name	Single Mounting Kit
Number of Poles	3
Suitable For	EF45
Connecting Capacity Main Circuit	Flexible with Ferrule 1x 2.5 ... 10 mm ² Flexible with Insulated Ferrule 1x 2.5 ... 10 mm ² Flexible 1x 2.5 ... 10 mm ² Rigid 1x 2.5 ... 16 mm ²
Wire Stripping Length	Main Circuit 15 mm
Tightening Torque	Main Circuit 0.8 ... 1.5 N·m
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
Recommended Screw Driver	Pozidriv 2
Connecting Capacity Main Circuit UL/CSA	Flexible 1x 14-6 AWG Stranded 1x 14-6 AWG
RoHS Status	Following EU Directive 2011/65/EU
Tightening Torque UL/CSA	Main Circuit 7 ... 13 in·lb

Classifications

ETIM 5.0	EC002498 - Accessories for low-voltage switch technology
ETIM 6.0	EC002498 - Accessories for low-voltage switch technology
ETIM 7	EC002498 - Accessories for low-voltage switch technology
eClass	7.0 27379201
ETIM 4	EC002498 - Accessories for low-voltage switch technology

Dimensions

Product Net Width	45 mm
Product Net Height	130 mm
Product Net Weight	0.1kg

by ABB

Dimensions

Product Net Depth / Length	98 mm
----------------------------	-------

Package Information

Package Level 1 Units	1 piece
Package Level 1 Width	135 mm
Package Level 1 Depth / Length	48 mm
Package Level 1 Gross Weight	0.124 kg
Package Level 1 EAN	4013614493393
Package Level 1 Height	104 mm

Ordering

ECN	N
Customs Tariff Number	85389099
ECCN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)