

Alternate Catalog No. DB25/32A
Catalog No. 1SAZ201108R0002

Description: DB25/32A Single Mounting Kit

UPC No 4013614237744

Home > Contactors & Starters > Overload Relays

DB25/32A Single monting kit for TA25DU

Descriptors

Category	Overload Relays

Specifications

Product Name	Single Mounting Kit
Rated Operational Voltage	Main Circuit 690 V AC
Rated Impulse Withstand Voltage	Main Circuit 6 kV
Rated Insulation Voltage	690 V
Number of Poles	3
Rated Frequency	Main Circuit 50Hz Main Circuit 60 Hz
Rated Operational Current AC-3	32 A
Pollution Degree	3
Suitable For	TA25DU
Standards	UL 60947-1 UL 60947-4-1
Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Ampere Rating UL/CSA	32 A
Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	Q

Classifications

ETIM 5.0	EC002498 - Accessories for low-voltage switch technology
ETIM 6.0	EC002498 - Accessories for low-voltage switch technology
ETIM 7	EC002498 - Accessories for low-voltage switch technology
eClass	7.0 27379201
ETIM 4	EC002498 - Accessories for low-voltage switch technology

Dimensions

Product Net Width	44 mm
Product Net Height	84.5 mm

Dimensions

Product Net Weight	0.08kg
Product Net Depth / Length	85.8 mm

Package Information

Package Level 1 Units	10 piece
Package Level 1 Width	238 mm
Package Level 1 Depth / Length	82 mm
Package Level 1 Gross Weight	0.905 kg
Package Level 1 EAN	4013614515125
Package Level 1 Height	140 mm

Ordering

ECN	N
Customs Tariff Number	85389099
ECCN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)