

## Alternate Catalog No. DX25 Catalog No. 1SAZ201307R0002

**Description:** DX25 Terminal Block

**UPC No** 4013614237928

**Home > Contactors & Starters > Overload Relays**

DX25 Terminal Block



### Descriptors

Category	Overload Relays
----------	-----------------

### Specifications

Product Name	Terminal Block
Rated Insulation Voltage	690 V
Number of Poles	3
Pollution Degree	3
Suitable For	TA25DU DB25
Connecting Capacity Main Circuit	Rigid 1x 1.5 ... 10 mm <sup>2</sup> Flexible with Ferrule 1x 1.5 ... 6 mm <sup>2</sup> Flexible 1x 1.5 ... 6 mm <sup>2</sup>
Tightening Torque	Main Circuit 2.5 ... 3.2 N·m
Standards	UL 60947-1 UL 60947-4-1
Recommended Screw Driver	Pozidriv 2
Connecting Capacity Main Circuit UL/CSA	Stranded 1x 10 ... 8 AWG Flexible 1x 10 ... 8 AWG
Ambient Air Temperature	Operation -25 ... +55 °C
Tightening Torque UL/CSA	Main Circuit 20 in·lb

### Classifications

ETIM 5.0	EC002498 - Accessories for low-voltage switch technology
ETIM 6.0	EC002498 - Accessories for low-voltage switch technology
ETIM 7	EC002498 - Accessories for low-voltage switch technology
eClass	7.0 27379201
ETIM 4	EC002498 - Accessories for low-voltage switch technology

### Dimensions

Product Net Width	39 mm
Product Net Height	27 mm
Product Net Weight	0.03kg
Product Net Depth / Length	29 mm

**by ABB**

### Package Information

Package Level 1 Units	1 piece
Package Level 1 Width	98 mm
Package Level 1 Depth / Length	47 mm
Package Level 1 Gross Weight	0.32 kg
Package Level 1 EAN	4013614237928
Package Level 1 Height	82 mm

### Ordering

ECN	N
Customs Tariff Number	85369010
ECCN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)