

Representative Image

Alternate Catalog No. OA1G10
Catalog No. 1SCA022353R4970

Description: 1-NO AUX SW OT/OS

UPC No 6417019102443

Home > Switches & Disconnects > Disconnect & Safety Switches > Disconnect Switches > Rotary Disconnects

OA1G10 AUXILIARY CONTACT

Descriptors

Category	Rotary Disconnects

Specifications

Product Name	Accessories
Accessory Type	Auxiliary contacts
Accessory Sub Type	AUXILIARY CONTACT
Product Main Type	OA1G

Specifications

Suitable For	OT16 OT25 OT40 OTM40 OT63 OTM63 OT80 OTM80 OT100 OTM100 OT125 OTM125 OT160G OT200 OTM200 OT250 OTM250 OT315 OTM315 OT400 OTM400 OT500 OT630 OTM630 OT800 OTM800 OT1000 OTM1000 OT1250 OTM1250 OT1600 OTM1600 OT2000 OTM2000 OT2500 OTM2500 OT3200 OT4000 OT200U OT400U OT600U OT800U OT1200U OTDC100 OTDC160 OTDC200 OTDC250 OTDC315 OTDC400 OTDC500 OTDC630 OTDC800 OTDC100U OTDC200U OTDC250U OTDC320U OTDC400U OTDC600U OT16F_C OT25F_C OT40F_C OT63F_C OT80F_C OT125F_C OT100F_C OT160_C OT160_CF OT160_CL OT200_C OT200_CF OT200_CL OT250_C OT250_CF

Specifications

Suitable For	OT250_CL OT315_C OT315_CF OT315_CL OT400_C OT400_CF OT400_CL OT630_C OT630_CF OT630_CL OT800_C OT800_CF OT800_CL OT1000_C OT1000_CL OT1250_C OT1250_CL OT1600_C OT1600_CL OT2000_C OT2000_CL OT2500_C OT2500_CL OT3200_C OT200U_C OT400U_C OT600U_C OT800U_C OTM40_CM OTM63_CM OTM80_CM OTM100_CM OTM125_CM OTM160_CM OTM200_CM OTM250_CM OTM315_CM OTM400_CM OTM630_CM OTM800_CM OTM1000_CM OTM1250_CM OTM1600_CM OTM2000_CM OTM2500_CM OTM3200_CM OTM160_C_D OTM200_C_D OTM250_C_D OTM315_C_D OTM400_C_D OTM630_C_D OTM800_C_D OTM1000_C_D OTM1250_C_D OTM1600_C_D OT160_Y OT200_Y OT250_Y OT315_Y OT400_Y OT630_Y OT800_Y OTM160_Y OTM200_Y OTM250_Y OTM315_Y OTM400_Y OTM630_Y OTM800_Y OS16 OS20 OS25

Specifications

Suitable For	OS32 OS40 OS63G OSM32 OS50 OSM50 OSM63G OS100G OSM100G OS160G OS125G OSM125G OSM160G OS200 OSM200 OS250 OSM250 OS315 OSM315 OS400 OSM400 OS630 OSM630 OS800 OSM800 OS1250 OSM1250 OS30 OS60 OS600 OS1200 OTM2000_C_D OTM2500_C_D OTM3200_C_D OTDC1000 OTDC1250 OTDC1600 OTDC180U OTDC800U OTDC1000U OTM40_C_D OTM63_C_D OTM125_C_D OX200 OX250 OX315 OX400 OX630 OX800 OX1000 OX1250 OX1600
Rated Voltage (V)	690 V
Quantity / Count	1