



**Alternate Catalog No. OA1G10**  
**Catalog No. 1SCA022353R4970**

**Description: 1-NO AUX SW OT/OS**

**UPC No 6417019102443**

**Home > Switches & Disconnects > Disconnect & Safety Switches > Disconnect Switches > Rotary Disconnects**

OA1G10 AUXILIARY CONTACT

**Descriptors**

Category	Rotary Disconnects
----------	--------------------

**Specifications**

Product Name	Accessories
Accessory Type	Auxiliary contacts
Accessory Sub Type	AUXILIARY CONTACT
Product Main Type	OA1G

## Specifications

Suitable For

OT16  
OT25  
OT40  
OTM40  
OT63  
OTM63  
OT80  
OTM80  
OT100  
OTM100  
OT125  
OTM125  
OT160G  
OT200  
OTM200  
OT250  
OTM250  
OT315  
OTM315  
OT400  
OTM400  
OT500  
OT630  
OTM630  
OT800  
OTM800  
OT1000  
OTM1000  
OT1250  
OTM1250  
OT1600  
OTM1600  
OT2000  
OTM2000  
OT2500  
OTM2500  
OT3200  
OT4000  
OT200U  
OT400U  
OT600U  
OT800U  
OT1200U  
OTDC100  
OTDC160  
OTDC200  
OTDC250  
OTDC315  
OTDC400  
OTDC500  
OTDC630  
OTDC800  
OTDC100U  
OTDC200U  
OTDC250U  
OTDC320U  
OTDC400U  
OTDC600U  
OT16F\_C  
OT25F\_C  
OT40F\_C  
OT63F\_C  
OT80F\_C  
OT125F\_C  
OT100F\_C  
OT160\_C  
OT160\_CF  
OT160\_CL  
OT200\_C  
OT200\_CF  
OT200\_CL  
OT250\_C  
OT250\_CF

**Specifications**

Suitable For

- OT250\_CL
- OT315\_C
- OT315\_CF
- OT315\_CL
- OT400\_C
- OT400\_CF
- OT400\_CL
- OT630\_C
- OT630\_CF
- OT630\_CL
- OT800\_C
- OT800\_CF
- OT800\_CL
- OT1000\_C
- OT1000\_CL
- OT1250\_C
- OT1250\_CL
- OT1600\_C
- OT1600\_CL
- OT2000\_C
- OT2000\_CL
- OT2500\_C
- OT2500\_CL
- OT3200\_C
- OT200U\_C
- OT400U\_C
- OT600U\_C
- OT800U\_C
- OTM40\_CM
- OTM63\_CM
- OTM80\_CM
- OTM100\_CM
- OTM125\_CM
- OTM160\_CM
- OTM200\_CM
- OTM250\_CM
- OTM315\_CM
- OTM400\_CM
- OTM630\_CM
- OTM800\_CM
- OTM1000\_CM
- OTM1250\_CM
- OTM1600\_CM
- OTM2000\_CM
- OTM2500\_CM
- OTM3200\_CM
- OTM160\_C\_D
- OTM200\_C\_D
- OTM250\_C\_D
- OTM315\_C\_D
- OTM400\_C\_D
- OTM630\_C\_D
- OTM800\_C\_D
- OTM1000\_C\_D
- OTM1250\_C\_D
- OTM1600\_C\_D
- OT160\_Y
- OT200\_Y
- OT250\_Y
- OT315\_Y
- OT400\_Y
- OT630\_Y
- OT800\_Y
- OTM160\_Y
- OTM200\_Y
- OTM250\_Y
- OTM315\_Y
- OTM400\_Y
- OTM630\_Y
- OTM800\_Y
- OS16
- OS20
- OS25

**Specifications**

<p>Suitable For</p>	<p>OS32  OS40  OS63G  OSM32  OS50  OSM50  OSM63G  OS100G  OSM100G  OS160G  OS125G  OSM125G  OSM160G  OS200  OSM200  OS250  OSM250  OS315  OSM315  OS400  OSM400  OS630  OSM630  OS800  OSM800  OS1250  OSM1250  OS30  OS60  OS600  OS1200  OTM2000_C_D  OTM2500_C_D  OTM3200_C_D  OTDC1000  OTDC1250  OTDC1600  OTDC180U  OTDC800U  OTDC1000U  OTM40_C_D  OTM63_C_D  OTM125_C_D  OX200  OX250  OX315  OX400  OX630  OX800  OX1000  OX1250  OX1600</p>
<p>Rated Voltage (V)</p>	<p>690 V</p>
<p>Quantity / Count</p>	<p>1</p>