



Alternate Catalog No. OA3G01AU
Catalog No. 1SCA022819R5260

Description: 1NC AUX SWITCH OT16-125 GOLD

UPC No 6417019279688

Home > Switches & Disconnects > Disconnect & Safety Switches > Disconnect Switches > Rotary Disconnects

OA3G01AU AUXILIARY CONTACT

Descriptors

Category	Rotary Disconnects
----------	--------------------

Specifications

Product Name	Accessories
Accessory Type	Auxiliary contacts
Accessory Sub Type	AUXILIARY CONTACT
Product Main Type	OA3G

Specifications

Suitable For

OT160
OTM160
OT200
OTM200
OT250
OTM250
OT315
OTM315
OT400
OTM40
OTM400
OT500
OT630
OTM63
OTM630
OT800
OTM80
OTM800
OT1000
OTM100
OTM1000
OT1250
OTM125
OTM1250
OT1600
OTM1600
OT2000
OTM2000
OT2500
OTM2500
OT3200
OT4000
OT200U
OT400U
OT600U
OT800U
OT1200U
OTDC100
OTDC160
OTDC200
OTDC250
OTDC315
OTDC400
OTDC500
OTDC630
OTDC800
OTDC100U
OTDC200U
OTDC250U
OTDC320U
OTDC400U
OTDC600U
OT160_C
OT160_CF
OT160_CL
OT200_C
OT200_CF
OT200_CL
OT250_C
OT250_CF
OT250_CL
OT315_C
OT315_CF
OT315_CL
OT400_C
OT400_CF
OT400_CL
OT630_C
OT630_CF
OT630_CL
OT800_C
OT800_CF
OT800_CL

Specifications

Suitable For

- OT1000_C
- OT1000_CL
- OT1250_C
- OT1250_CL
- OT1600_C
- OT1600_CL
- OT2000_C
- OT2000_CL
- OT2500_C
- OT2500_CL
- OT3200_C
- OT200U_C
- OT400U_C
- OT600U_C
- OT800U_C
- OTM160_CM
- OTM200_CM
- OTM250_CM
- OTM315_CM
- OTM400_CM
- OTM630_CM
- OTM800_CM
- OTM1000_CM
- OTM1250_CM
- OTM1600_CM
- OTM2000_CM
- OTM2500_CM
- OTM3200_CM
- OTM160_C_D
- OTM200_C_D
- OTM250_C_D
- OTM315_C_D
- OTM400_C_D
- OTM630_C_D
- OTM800_C_D
- OTM1000_C_D
- OTM1250_C_D
- OTM1600_C_D
- OT160_Y
- OT200_Y
- OT250_Y
- OT315_Y
- OT400_Y
- OT630_Y
- OT800_Y
- OTM160_Y
- OTM200_Y
- OTM250_Y
- OTM315_Y
- OTM400_Y
- OTM630_Y
- OTM800_Y
- OS16
- OS20
- OS25
- OS32
- OS40
- OS63
- OSM32
- OS50
- OSM50
- OSM63
- OS100
- OSM100
- OS160
- OS125
- OSM125
- OSM160
- OS200
- OSM200
- OS250
- OSM250
- OS315

Specifications

Suitable For	OSM315 OS400 OSM400 OS630 OSM630 OS800 OSM800 OS1250 OSM1250 OS30 OS60 OS600 OS1200 OTM2000_C_D OTM2500_C_D OTM3200_C_D OX200 OX250 OX315 OX400 OX630 OX800 OX1000 OX1250 OX1600
Rated Voltage (V)	690 V
Quantity / Count	1