

Representative Image

# Alternate Catalog No. AF400F-30-11-70
# Catalog No. 1SFL577001R9103

**Description: AF400F-30-11 100-250V AC/DC Contactor**

**UPC No 7320500223130**

**Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors**

A 3-pole contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 1000 V. Operated with datasheet specified control voltages. Equipped with auxiliary contacts.

## Descriptors

| | |
|---|---|
| Category | AF Contactors |
| Block Contactor Type | 3-Pole Contactor |

## Specifications

| | |
|---|---|
| Product Type | AF |
| General Use Rating UL/CSA | (600 V AC) 550 A |
| Object Classification Code | Q |
| Terminal Type | Main Circuit: Bars |
| Rated Control Circuit Voltage | 50 Hz /60 Hz DC Operation 100 ... 250 V |
| Number of Main Contacts NO | 3 |
| Number of Main Contacts NC | 0 |
| RoHS Status | Following EU Directive 2011/65/EU |
| Rated Operational Power AC-3 | (1000 V) 220 KWT<br>(220 / 230 / 240 V) 110 KWT<br>(380 / 400 V) 200 KWT<br>(415 V) 220 KWT<br>(440 V) 220 KWT<br>(500 V) 250 KWT<br>(690 V) 315 KWT |
| Horsepower Rating UL/CSA | (200 V AC) Three Phase 125 hp<br>(208 V AC) Three Phase 125 hp<br>(220 ... 240 V AC) Three Phase 150 hp<br>(440 ... 480 V AC) Three Phase 350 hp<br>(550 ... 600 V AC) Three Phase 400 hp |
| Rated Operational Current AC-3 | (1000 V) 55 °C 155 A<br>(220 / 230 / 240 V) 55 °C 400 A<br>(380 / 400 V) 55 °C 400 A<br>(415 V) 55 °C 400 A<br>(440 V) 55 °C 400 A<br>(500 V) 55 °C 400 A<br>(690 V) 55 °C 350 A |
| Mechanical Durability | 3 million |
| Screw Terminal Type | Main Circuit: Bars |

## Classifications

| | |
|---|---|
| ETIM 4 | EC000066 - Magnet contactor, AC-switching |
| ETIM 6.0 | EC000066 - Power contactor, AC switching |

by ABB

## Classifications

| | |
|---|---|
| ETIM 7 | EC000066 - Power contactor, AC switching |
| IDEA Granular Category Code (IGCC) | 4755 >> Contactors |
| ETIM 5.0 | EC000066 - Magnet contactor, AC-switching |

## Dimensions

| | |
|---|---|
| Product Net Weight | 10.6 kg |
| Product Net Depth / Length | 216 mm |
| Product Net Width | 186 mm |
| Product Net Height | 278 mm |

## Package Information

| | |
|---|---|
| Package Level 1 Width | 280 mm |
| Package Level 1 Height | 310 mm |
| Package Level 1 Depth / Length | 375 mm |
| Package Level 1 Units | box 1 piece |
| Package Level 1 Gross Weight | 12 kg |

## Ordering

| | |
|---|---|
| Minimum Order Quantity | 1 |
| Customs Tariff Number | 85364900 |