



360°

Representative Image

## Alternate Catalog No. AF460W-30-01E70 Catalog No. 1SFL597027R9100

**Description: AF460W-30-01 100-250V Contactor**
**UPC No 7320500256558**
**Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors**

A 3-pole contactor suitable for Welding applications such as Motor starting, Isolation, By-pass and Distribution application up to max 1000 V. Operated with datasheet specified control voltages. Equipped with no auxiliary contacts .

### Descriptors

Category	AF Contactors
Block Contactor Type	3-Pole Contactor

### Specifications

Product Type	AF
General Use Rating UL/CSA	(600 V AC) 550 A
Object Classification Code	Q
Rated Control Circuit Voltage	50 Hz /60 Hz DC Operation 100 ... 250 V
RoHS Status	Following EU Directive 2011/65/EU
Mechanical Durability	3000000 cycle
Maximum Mechanical Switching Frequency	300 cycles per hour

### Classifications

ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 6.0	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
IDEA Granular Category Code (IGCC)	4755 >> Contactors
ETIM 5.0	EC000066 - Magnet contactor, AC-switching

### Dimensions

Product Net Weight	10.6 kg
Product Net Depth / Length	216 mm
Product Net Width	186 mm
Product Net Height	278 mm

### Package Information

Package Level 1 Width	280 mm
Package Level 1 Depth / Length	375 mm
Package Level 1 Units	box 1 piece

**by ABB**

**Ordering**

Minimum Order Quantity	1
------------------------	---

---