

Catalog No. 1SNA645018R0300

Description: RB111R-24VUC Interface relay R600 1n/o,A1-A2=24VAC/DC,5-250VAC/60mA-6A, with integrated output contact protection

UPC No 4013614507861

Home > Controls & Protective Relays > Interface Relays & Optocouplers



Representative Image

Descriptors

Category	Interface Relays & Optocouplers
----------	---------------------------------

Specifications

Function	Boxed interface relay R600
Rated Control Supply Voltage	24 V AC / DC
Output Signal	5 ... 250VAC / 60mA ... 6A
Terminal Type	Screw Terminals
Output	1 n/o contact
Contact material	silver-tin-oxide (AgSnO ₂)
Product Main Type	R600
Sub-Function	Relay with built in LED and RC circuit
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	K

Classifications

ETIM 4	EC001437 - Switching relay
ETIM 5.0	EC001437 - Switching relay
ETIM 6.0	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
eClass	7.0 27371601

Dimensions

Product Net Width	12 mm
Product Net Height	67.5 mm
Product Net Depth / Length	70 mm
Product Net Weight	0.04kg

Package Information

Package Level 1 Units	5 piece
-----------------------	---------

by ABB

Package Information

Package Level 1 Width	73 mm
Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.24 kg
Package Level 1 EAN	3472596450182

Ordering

Minimum Order Quantity	5
Customs Tariff Number	85364900
ECCN	N
ECN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)
ABB Business Unit	ELSP - Smart Power