



Representative Image

Catalog No. 1SVR405521R1100

Description: CR-S006/024VDC1SS Socket 1c/o, A1-A2=6-24VDC, 250VAC

UPC No 4013614499180

Home > Controls & Protective Relays > Interface Relays & Optocouplers

Descriptors

Category	Interface Relays & Optocouplers
----------	---------------------------------

Specifications

Function	Accessory for interface relays CR-S
Rated Control Supply Voltage	6 ... 24 V DC
Terminal Type	Screw Terminals
Product Main Type	CR-S
Sub-Function	Socket
Ambient Air Temperature	Operation -40 ... +70 °C Storage 0 ... +40 °C
RoHS Status	Following EU Directive 2011/65/EU
Connecting Capacity UL/CSA	Flexible 14 AWG Rigid 14 AWG
Tightening Torque UL/CSA	4.42 in-lb
Object Classification Code	K

Classifications

ETIM 4	EC001456 - Relay socket
ETIM 5.0	EC001456 - Relay socket
ETIM 6.0	EC001456 - Relay socket
ETIM 7	EC001456 - Relay socket
eClass	7.0 27371603

Dimensions

Product Net Width	6.3 mm
Product Net Height	76.4 mm
Product Net Depth / Length	88.5 mm
Product Net Weight	0.025 kg

Package Information

Package Information

Package Level 1 Units	10 piece
Package Level 1 Width	93 mm
Package Level 1 Height	81 mm
Package Level 1 Depth / Length	66 mm
Package Level 1 Gross Weight	0.26 kg
Package Level 1 EAN	4013614486319

Ordering

Minimum Order Quantity	10
Customs Tariff Number	85369010
ECCN	N
ECN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)
ABB Business Unit	ELSP - Smart Power