



Catalog No. 1SVR427060R2000

Description: CP-B 24/20.0 Buffer module 24 V / 20 A, energy storage 8000 Ws

UPC No 4016779782579

Home > Controls & Protective Relays > Power Supplies

CP-B 24/20.0 Buffer module 24 V / 20 A, energy storage 8000 Ws

Descriptors

Category	Power Supplies
----------	----------------

Specifications

Product Main Type	CP-B
Number of phases	1
Input Voltage	24 V DC
Output Voltage	24 V DC
Output Current	20 A
Output Power	480 W
Function	Buffer module
Degree of Protection	Housing Terminals IP20 IP20
Pollution Degree	2
Minimum Mounting Distance	Other Device Same Type, Vertical 80 mm
Mounting Position	Position 1
Standards	CAN/CSA C22.2 No.107.1 EN 50178 EN 50581 EN 55011 IEC/EN 60950-1 IEC/EN 61000-6-2 IEC/EN 61000-6-4 IEC/EN 62040-2 UL508
Ambient Air Temperature	Operation -40 ... +60 °C Storage -40 ... +60 °C
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	C

Classifications

ETIM 4	EC002540 - DC-power supply
ETIM 5.0	EC002540 - DC-power supply
ETIM 6.0	EC002540 - DC-power supply
ETIM 7	EC002540 - DC-power supply

by ABB

Dimensions

Product Net Width	84 mm
Product Net Height	198 mm
Product Net Depth / Length	216 mm
Product Net Weight	2.2 kg

Package Information

Package Level 1 Width	320 mm
Package Level 1 Depth / Length	335 mm
Package Level 1 Height	150 mm
Package Level 1 Gross Weight	3 kg
Package Level 1 EAN	4016779782579
Package Level 1 Units	1 piece

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85044082
ECCN	N
ECN	N