



Catalog No. 2521-G

Description: PVC CTD CORD CONN, HUB 1/2IN GRAY

UPC No 704508030360

Home > Cable Protection Systems > Ocal > Cable gland connector

PVC Coated Strain Relief Cord Connector, Cable Size .250-.375, Hub Size 1/2 Inch, Throat Diameter 9/16 Inch, Gray

Descriptors

Category	Cable gland connector
Special Features	PVC Coated for Corrosion Resistance
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead

Specifications

Conductor Range	0.250-0.375 Inch
Material	Zinc Die Cast
Color	Gray
Temperature Rating	105 C
Environmental Conditions	Suitable for Hazardous Locations

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	1/2 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000441 Cable gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Suitable for cable diameter	6.35-9.525 mm
Material	Metal

by ABB

ETIM	EC000441 Cable gland
Material quality	Other
Surface protection	Other
Colour	Light grey
Model	Straight