



Catalog No. 2530-G

Description: PVC CTD CORD CONN, HUB 3/4IN GRAY

UPC No 704508016609

Home > Cable Protection Systems > Ocal > Cable gland connector

PVC Coated Strain Relief Cord Connector, Cable Size 0.125-0.250, Gray

Descriptors

Category	Cable gland connector
Special Features	PVC Coated for Corrosion Resistance
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead

Specifications

Conductor Range	0.125-0.250 Inch
Material	Zinc Die Cast
Color	Gray
Temperature Rating	105 C
Environmental Conditions	Suitable for Hazardous Locations

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	3/4 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000441 Cable gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Suitable for cable diameter	3.175-6.35 mm
Material	Metal

by ABB

ETIM	EC000441 Cable gland
Material quality	Other
Surface protection	Other
Colour	Light grey
Model	Straight