



Catalog No. 2534-G

Description: PVC CTD CORD CONN, HUB 3/4IN GRY

UPC No 704508029067

Home > Cable Protection Systems > Ocal > Cable gland connector

PVC Coated Strain Relief Cord Connector, Cable Size .500-.625, Hub Size 3/4 Inch, Throat Diameter 13/16 Inch, Gray

Descriptors

Category	Cable gland connector
Special Features	PVC Coated for Corrosion Resistance
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead

Specifications

Conductor Range	0.500-0.625 Inch
Material	Zinc Die Cast
Color	Gray
Temperature Rating	105 C
Environmental Conditions	Suitable for Hazardous Locations

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	3/4 Inch
------	----------

ETIM	EC000441 Cable gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Suitable for cable diameter	12.70-15.875 mm
Material	Metal
Material quality	Other
Surface protection	Other
Colour	Light grey
Model	Straight

by ABB