



Catalog No. 2564-G

Description: PVC CTD CORD CONN, HUB 1-1/2IN GRAY

UPC No 704508018733

Home > Cable Protection Systems > Ocal > Cable gland connector

PVC Coated Strain Relief Cord Connector, Cable Size 1.187-1.375, Hub Size 1-1/2 Inch, Throat Diameter 1-27/16 Inch, Gray

Descriptors

Category	Cable gland connector
Special Features	PVC Coated for Corrosion Resistance
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead

Specifications

Conductor Range	1.187-1.375 Inch
Material	Zinc Die Cast
Color	Gray
Temperature Rating	105 C
Environmental Conditions	Suitable for Hazardous Locations

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	1-1/2 Inch
------	------------

ETIM	EC000441 Cable gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/2 inch
Suitable for cable diameter	30.15-34.925 mm
Material	Metal
Material quality	Other
Surface protection	Other
Colour	Light grey
Model	Straight

by ABB