



Catalog No. 2585-G

Description: PVC CTD CORD CONN, HUB 2-1/2IN GRAY

UPC No 704508017064

Home > Cable Protection Systems > Ocal > Cable gland connector

PVC Coated Strain Relief Cord Connector, Cable Size 1.937-2.187, Hub Size 2-1/2 Inch, Throat Diameter 2 Inch, Gray

Descriptors

Category	Cable gland connector
Special Features	PVC Coated for Corrosion Resistance
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead

Specifications

Conductor Range	1.937-2.187 Inch
Material	Zinc Die Cast
Color	Gray
Temperature Rating	105 C
Environmental Conditions	Suitable for Hazardous Locations

Classifications

Brand Name	Ocal
Standard	UL E13938, RoHS, Coast Guard CG293

Dimensions

Size	2-1/2 Inch
------	------------

ETIM	EC000441 Cable gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	2 1/2 inch
Suitable for cable diameter	49.20-55.55 mm
Material	Metal
Material quality	Other
Surface protection	Other
Colour	Light grey
Model	Straight

by ABB