



**Alternate Catalog No. S802U-K10**  
**Catalog No. 2CCS862017R0427**

**Description: MCB S800 2P K 10A**

**UPC No 7612271214012**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

S802U-K10 2 Pole K Characteristic 10A 50kA 240/415VAC High Performance Circuit Breaker HPCB

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(240 V AC) 50 kA
Number of Poles	2
Power Loss	1.5 W
Product Main Type	S800U
Rated Current	10 A
Rated Ultimate Short-Circuit Breaking Capacity	(415 V AC) 50 kA
Rated Voltage (V)	(240 V AC)
Standards	IEC/EN 60947-2 UL 489 CSA C22.2 No.5
Tripping Characteristic	K