

Representative Image

Alternate Catalog No. S802U-K40
Catalog No. 2CCS862017R0557

Description: MCB S800 2P K 40A

UPC No 7612271214210

Home > Modular DIN Rail Products > Mini Circuit breakers

S802U-K40 2 Pole K Characteristic 40A 50kA 240/415VAC High Performance Circuit Breaker HPCB

Descriptors

Category	Mini Circuit breakers

Specifications

Interrupting Rating acc. to UL489	50 kA
Number of Poles	2
Power Loss	3.7 W
Product Main Type	S800U
Rated Current	40 A
Rated Ultimate Short-Circuit Breaking Capacity	(415 V AC) 50 kA
Rated Voltage (V)	(240 V AC)
Standards	IEC/EN 60947-2 UL 489
Tripping Characteristic	K