

Representative Image

Alternate Catalog No. SU201M-C32
Catalog No. 2CDS271337R0324

Description: UL489 MCB 1P C 32A 480/277

UPC No 4016779930918

Home > Modular DIN Rail Products > Mini Circuit breakers

SU201M-C32 Miniature Circuit Breaker C-Char., 10kA, 32A, 1P UL489

Descriptors

Category	Mini Circuit breakers

Specifications

Interrupting Rating acc. to UL489	(277 V AC) 10 kA (48 V DC) 10 kA
Number of Poles	1
Power Loss	3,7 W at Rated Operating Conditions per Pole 3,7 W
Product Main Type	SU200M
Rated Current	32 A
Rated Ultimate Short-Circuit Breaking Capacity	(230 V AC) 15 kA
Rated Voltage (V)	(277 V AC) (48 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	C