

Representative Image

# Alternate Catalog No. SU201M-K15
# Catalog No. 2CDS271337R0457

**Description: UL489 MCB 1P K 15A 480/277**

**UPC No 4016779930116**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU201M-K15 Miniature Circuit Breaker K-Char., 10kA, 15A, 1P UL489

## Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

## Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (277 V AC) 10 kA<br>(48 V DC) 10 kA |
| Number of Poles | 1 |
| Power Loss | 2,4 W<br>at Rated Operating Conditions per Pole 2,4 W |
| Product Main Type | SU200M |
| Rated Current | 15 A |
| Rated Ultimate Short-Circuit Breaking Capacity | (230 V AC) 15 kA |
| Rated Voltage (V) | (277 V AC)<br>(48 V DC) |
| Standards | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489 |
| Tripping Characteristic | K |