



Representative Image

**Alternate Catalog No. SU201M-K20**  
**Catalog No. 2CDS271337R0487**

**Description:** UL489 MCB 1P K 20A 480/277

**UPC No** 4016779930130

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU201M-K20 Miniature Circuit Breaker K-Char., 10kA, 20A, 1P UL489

**Descriptors**

Category	Mini Circuit breakers
----------	-----------------------

**Specifications**

Interrupting Rating acc. to UL489	(277 V AC) 10 kA (48 V DC) 10 kA
Number of Poles	1
Power Loss	2,5 W at Rated Operating Conditions per Pole 2,5 W
Product Main Type	SU200M
Rated Current	20 A
Rated Ultimate Short-Circuit Breaking Capacity	(230 V AC) 15 kA
Rated Voltage (V)	(277 V AC) (48 V DC)
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Tripping Characteristic	K