



Representative Image

Alternate Catalog No. SU201M-K32
Catalog No. 2CDS271337R0537

Description: UL489 MCB 1P K 32A 480/277

UPC No 4016779930161

Home > Modular DIN Rail Products > Mini Circuit breakers

SU201M-K32 Miniature Circuit Breaker K-Char., 10kA, 32A, 1P UL489

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|--|---|
| Interrupting Rating acc. to UL489 | (277 V AC) 10 kA (48 V DC) 10 kA |
| Number of Poles | 1 |
| Power Loss | 3,7 W at Rated Operating Conditions per Pole 3,7 W |
| Product Main Type | SU200M |
| Rated Current | 32 A |
| Rated Ultimate Short-Circuit Breaking Capacity | (230 V AC) 15 kA |
| Rated Voltage (V) | (277 V AC) (48 V DC) |
| Standards | CSA 22.2 No. 5 IEC/EN 60947-2 UL 489 |
| Tripping Characteristic | K |