

Representative Image

## Alternate Catalog No. SU201MR-K0.2
## Catalog No. 2CDS271347R0087

**Description: MCB SU200MR RTT 1P K 0.2A BCP**

**UPC No 4016779956192**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU201MR-K0.2 MCB K-Char., 10kA, 0.2A, 1P, RTT UL 489, Ring Cable Lug

### Descriptors

| | |
|---|---|
| Category | Mini Circuit breakers |

### Specifications

| | |
|---|---|
| Interrupting Rating acc. to UL489 | (277 V AC) 10 kA<br>(48 V DC) 10 kA |
| Number of Poles | 1 |
| Power Loss | at Rated Operating Conditions per Pole 1.7 W |
| Product Main Type | SU200MR |
| Rated Current | 0.20 A |
| Rated Voltage (V) | (277 V AC)<br>(48 V DC) |
| Tripping Characteristic | K |