



Alternate Catalog No. SU201MR-K0.3
Catalog No. 2CDS271347R0117

Description: MCB SU200MR RTT 1P K 0.3A BCP

UPC No 4016779956215

Home > Modular DIN Rail Products > Mini Circuit breakers

SU201MR-K0.3 MCB K-Char., 10kA, 0.3A, 1P, RTT UL 489, Ring Cable Lug

Descriptors

| | |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

Specifications

| | |
|-----------------------------------|--|
| Interrupting Rating acc. to UL489 | (277 V AC) 10 kA (48 V DC) 10 kA |
| Number of Poles | 1 |
| Power Loss | at Rated Operating Conditions per Pole 1.7 W |
| Product Main Type | SU200MR |
| Rated Current | 0.30 A |
| Rated Voltage (V) | (277 V AC) (48 V DC) |
| Tripping Characteristic | K |