

Representative Image

Alternate Catalog No. SU201MR-K30
Catalog No. 2CDS271347R0527

Description: MCB SU200MR RTT 1P K 30A BCP

UPC No 4016779956550

Home > Modular DIN Rail Products > Mini Circuit breakers

SU201MR-K30 MCB K-Char., 10kA, 30A, 1P, RTT UL 489, Ring Cable Lug

Descriptors

Category	Mini Circuit breakers

Specifications

Interrupting Rating acc. to UL489	(277 V AC) 10 kA (48 V DC) 10 kA
Number of Poles	1
Power Loss	at Rated Operating Conditions per Pole 3.5 W
Product Main Type	SU200MR
Rated Current	30 A
Rated Voltage (V)	(277 V AC) (48 V DC)
Tripping Characteristic	K